

SLB4-G/N-X



38.5 38.5

Item number 49.7043-*

Insulated, rigid, \emptyset 4 mm, accepting spring-loaded \emptyset 4 mm plugs with rigid insulating sleeve. Machined brass. Insulation material UL94 V-0. The socket is screwed into pre-drilled panels of plastic, metal, etc. Threaded bolt M4 and soldering hole.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT III, 32 A / 600 V, CAT IV, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	20 21 22 23 24 25 26 27 28 29
Thread	M4
Test accessory acc. to	IEC EN 61010-2-030
Supplied assembly material	2x MU0,8D/M4N; MUR/M12x0,75
Remarks	Accessories: Tube spanner SS2; Tube spanner SS425
Approvals	UR