


ACR25-4N-39



Item number 64.2054-*

In-line, Ø 4 mm, with spring-loaded MULTILAM for self-assembly of test leads. Crimp connection.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 V, 32 A / 60 V, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 29
Optional color(s)	26 27
Outer diameter	8.0 mm
Test accessory acc. to	IEC EN 61010-031