

## SARK-4N-S10



42.5 42.5 65 42.5 665 42.5

Item number 66.1050- \*\*

Highly flexible. One end with in-line Ø 4 mm MULTILAM plug with rigid insulating sleeve. The other end with right-angled Ø 4 mm MULTILAM plug with rigid insulating sleeve.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT III, 19 A / 600 V, CAT IV, 19 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25
Optional color(s)	<mark>20</mark> 26 <b>27</b> 29
Lead lengths	100; 150; 200 cm
Lead insulation	SIL
Lead cross section	1,0 mm <sup>2</sup>
Test accessory acc. to	IEC EN 61010-031
User-Information	I 141
Approvals	UL, CE