


## SACR25-4A-46





Item number 66.2046-\*

In-line,  $\emptyset$  4 mm, with spring-loaded MULTILAM, for self-assembly of test leads. With rigid insulating sleeve. Crimp connection.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT II, 32 A / 600 V, CAT III, 32 A
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 29
Optional color(s)	<mark>20                                    </mark>
Outer diameter	9.6 mm
Test accessory acc. to	IEC EN 61010-031
Approvals	UR