

## XHB-5000





Item number 66.9427-\*

Insulated, rigid, Ø 4 mm for high voltages, to accept test leads XHM-5000 and XHL-5000. For safety reasons, the socket is not compatible with any other Ø 4 mm plugs in our range. Flat connecting tab 4.8 mm x 0.8 mm.

| Technical data                       |  |
|--------------------------------------|--|
| Diameter of plug system              | 4 mm   |
| Rated Values                         | 1000 V, CAT IV, 10 A   |
| Surface treatment electrical contact | Au   |
| Base material electrical contact     | CuZn   |
| Standard color(s) *                  | 21 22 23   |
| Thread                               | M12x0,75   |
| Test accessory acc. to               | IEC EN 61010-031   |
| User-Information                     | I 079  |
| Remarks                              | Rated voltage 5'000 V: Output voltage of test instruments, e.g. insulation testers |