


STÄUBLI

FLEXI-S/POAG-HK4





Item number 15.2010-*

Highly flexible, reinforced insulated stranded wire 4,0 mm².

Technical data	
Rated Values	AC 600 V, 42 A
Standard color(s) *	20
Lead insulation	PVC
Temperature range	-10 °C +70 °C
Strand design (n x Ø mm)	1036 x 0,07
Lead weigth	52.0 kg/km
Conductor diameter	3.0 mm
Cable diameter	4.8 mm
Insulation thickness	0.9 mm