




FLEXI-E/HK 1,0





Item number 60.7009-*

Highly flexible basic insulated stranded wire 1,0 mm².

Technical data	
Rated Values	AC 750 V, 19 A
Standard color(s) *	21 22 23 24 29
Lead insulation	PVC
Temperature range	-10 °C +70 °C
Strand design (n x Ø mm)	511 x 0,05
Lead weigth	14.0 kg/km
Conductor diameter	1.5 mm
Cable diameter	2.7 mm
Insulation thickness	0.6 mm
Approvals	CE, UKCA, EAC