




## FLEXI-S 10





Item number 60.7017-\*

Highly flexible stranded wire 10 mm<sup>2</sup> with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 73 A / DC 1500 V, 73 A
Standard color(s) *	20 21 22 23
Lead insulation	PVC
Temperature range	-10 °C +70 °C
Strand design (n x Ø mm)	2556 x 0,07
Lead weigth	120.0 kg/km
Conductor diameter	4.8 mm
Cable diameter	7.0 mm
Insulation thickness	1.1 mm
Approvals	UR, CE, UKCA, EAC