
STÄUBLI

SILI-S 4,0





Item number 61.7611-*

Highly flexible stranded wire 4,0 mm² with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 42 A / DC 1500 V, 42 A
Standard color(s) *	21 22 23 33
Lead insulation	SIL
Temperature range	-50°C +90°C
Strand design (n x Ø mm)	1036 x 0,07
Lead weigth	55.0 kg/km
Conductor diameter	3.0 mm
Cable diameter	5.4 mm
Insulation thickness	1.2 mm
Approvals	UR, CE, UKCA, EAC