


KS-4N-19



34.9



Item number 64.4012-*

Insulated, \emptyset 4 mm, made of brass. Plugs with spring-loaded MULTILAM contact technology. With insulated grip. At rear without in-line \emptyset 4 mm rigid sockets.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 V, 32 A / 60 V, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	2 <mark>0 21 22 23 24 25 26 27 28 29 30</mark>
Plug spacing	19 mm
Test accessory acc. to	IEC EN 61010-031
User-Information	I 099