


EPB-2N/S



Item number 63.9318-*

Insulated Ø 2 mm rigid. Machined brass. The socket is pressed into predrilled panels of plastic, metal etc. Solder pin Ø 1.5 mm.

Technical data	
Diameter of plug system	2 mm
Rated Values	30 V, 10 A / 60 V, 10 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 26 27 29
Test accessory acc. to	IEC EN 61010-2-030
Remarks	Accessories: Press-in tool MB2