



FLEXI-S 16



Item number 60.7018-*

Highly flexible stranded wire 16 mm² with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 98 A / DC 1500 V, 98 A
Standard color(s) *	20 21 22 23
Lead insulation	PVC
Temperature range	-10 °C ... +70 °C
Strand design (n x Ø mm)	4116 x 0,07
Lead weight	202.0 kg/km
Conductor diameter	6.1 mm
Cable diameter	8.5 mm
Insulation thickness	1.2 mm
Approvals	UR, CE, UKCA, EAC