



FLEXI-S 25



Item number 60.7020-*

Highly flexible stranded wire 25 mm² with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 129 A / DC 1500 V, 129 A
Standard color(s) *	20 21 22 23
Lead insulation	PVC
Temperature range	-10 °C ... +70 °C
Strand design (n x Ø mm)	6384 x 0,07
Lead weight	280.0 kg/km
Conductor diameter	7.0 mm
Cable diameter	9.8 mm
Insulation thickness	1.4 mm
Approvals	UR, CE, UKCA, EAC