


SILI-HV 1,0



Item number 61.7632-*

Super flexible, reinforced insulated stranded wire 1,0 mm².

Technical data	
Rated Values	AC 10000 V, 19 A
Standard color(s) *	21 22
Lead insulation	SIL
Temperature range	-50 °C ... +90 °C
Strand design (n x Ø mm)	259 x 0,07
Lead weighth	35.0 kg/km
Conductor diameter	1.4 mm
Cable diameter	5.5 mm
Insulation thickness	2.05 mm