

FAST MOVING TECHNOLOGY


STÄUBLI

TS2-80

4 axis industrial robot




reddot winner 2021



Characteristics

Load capacity	8.4 kg
Number of degrees of freedom	4
Repeatability XY - ISO 9283	± 0.015 mm
Repeatability Z - ISO 9283	± 0.004 mm
Repeatability Rz - ISO 9283	± 0.003°
Weight floor version	40 kg (vertical cable outlet: 36 kg)
Attachment methods	Floor / Ceiling (option)




Performance

Joint speed - axis 1	550°/s
Joint speed - axis 2	700°/s
Joint speed - axis 3	2100 mm/s
Joint speed - axis 4	2500°/s
Maximum inertia axis 4	0.1 kg.m²
Brakes	Axis 3 and 4
Cycles per minute *	200 (0.3s)

*Our programing and simulation software Staubli Robotics Suite 2019 enables an easy and pre-cise definition of your specific application cycle time. Cycle time for 25 mm - 300 mm - 25 mm motion pattern with 2 kg payload.


Standard U cycle 25-300-25 mm:



Work envelope and range of motion


Maximum reach between axis 1 and 4	800 mm
Minimum reach between axis 1 and 4	178 mm or 195 mm for ceiling version
Angular reach axis 1	360°
Angular reach axis 2	310°
Z Stroke	200 mm or 400 mm (option)
Angular reach axis 4	1000° ⁽¹⁾

(1) Under special conditions, consult us.




Installation environment

Working temperature according to NF EN 60 204-1	+5°C to +40°C
Humidity according to standard directive NF EN 60 204-1	30% to 95% max. non-condensing
Vertical cable outlet version	Available
Stäubli series controller	CS9
Pressurized version	Available
Cleanroom standard ISO 14644-1	Class ISO 6
Protection class according to EN 60529	IP34 standard / IP54 with ball screw cover / IP65 with ball screw cover and bellows



Base interface
(Horizontal cable outlet)




Base interface
(Vertical cable outlet)



User interface

	On forearm	On tool flange or tool changer (option)
Mechanical	NF EN ISO 9409-1 Ø 50 mm, 4 screws M6	
Pneumatic lines	3 direct pneumatic lines or 2 electro distributors in option : pressure 5/2 bi-stable or pressure 5/3 mono-stable “center closed” or vacuum 3/2 mono-stable or vacuum + pressure 3/2 mono-stable	
Electrical cables	10 electrical cables I/O + 1 multibus cable (4 wires) cat5e DIN M12 in the arm	3 electrical cables I/O + 1 multibus cable (4 wires) cat5e DIN M12 in the arm

Tool changer (option)




Automatic operation



Manual operation

Dimensions

Floor mounting



Ceiling mounting (vertical cable outlet)



Sensitive environment versions

Harsh (Automotive, Metal)	Available
ESD (ElectroStatic Discharge) version	Available
HE (Humid Environment) version	Available
Stericlean version	Available

Available options

Cover axis 3	for higher protection class
User harness from forearm to end of arm (flange or tool changer)	for higher connectivity
Flange interface	for easy integration
Tool changer interface	for more flexibility
Vertical cable outlet	for clean and clever integration
H1 oil and grease	for hygienic demands



● Stäubli Units ○ Representatives/Agents

Global presence of the Stäubli Group

www.staubli.com