


# CombiTac direct Main catalog

**Industrial Machinery & Equipment | Modular connectors**

EN



## STÄUBLI ELECTRICAL CONNECTORS

## Connections for Life



**Stäubli, as the international technology leader, offers innovative mechatronics solutions in its four divisions: Electrical Connectors, Fluid Connectors, Robotics, and Textile. At Stäubli Electrical Connectors, we develop advanced connection solutions based on the reliable MULTILAM contact technology.**

#### Together for reliable and safe connections

We know that you entrust us with the functionality of your applications and we work hard to ensure this every single day. Thanks to our high level of expertise, our extensive experience and the multiple successful co-operation with our partners, numerous new developments have originated at Stäubli Electrical Connectors and subsequently have become worldwide standards. This includes our MC4 connector portfolio for which we are today the global market

We create connections for life – and our customers are at the center of these connections. We are convinced that solid and stable partnerships directly contribute to our mutual success.

We take on the needs of our partners and deal with the most extraordinary challenges. As a result, we always create, sell and

support reliable and long-lasting products for markets with the highest productivity and safety requirements in close cooperation with our customers.

leader in photovoltaic. As the Stäubli original, the MC4 represents the result of our constant quest for innovation, quality and safety.

Further examples are the CombiTac modular connector system or the Quick Charging Connector (QCC) for automatic charging systems.

We ensure connections for life together with our long-standing customers in a wide range of industries from renewable energies, power transmission and distribution and E-mobility to industrial automation applica-

tions, railway and welding automation, test and measurement and medical devices.

Thus, developing reliable, efficient and safe solutions based on our proven MULTILAM contact technology, which guarantees a high service lifetime in addition to highly efficient power transmission.

# Applications and advantages



**CombiTac modular connectors combine various connection types in a single frame or housing and can be configured according to your exact specifications.**

Depending on your application needs, two types of CombiTac products are available, CombiTac direct and CombiTac uniq.

CombiTac direct is ideal for applications where fast tool-free assembly is required, and where it is necessary to combine electrical signal, power and pneumatic connections up to 10,000 mating cycles. Particularly in applications where a high quantity of modular connectors for low power and signals are needed, CombiTac direct offers significant economic advantages.

CombiTac uniq is designed for more demanding applications that require versatile long-life modular connector solutions, and where combination of power, signal, data, fiber optic, fluid and pneumatic connections are needed.

CombiTac uniq is 100 % customizable to meet exact technical and dimensional specifications, and thanks to the tried and tested MULTILAM Technology, its contacts can reach up to 100,000 mating cycles and current levels up to 300 A.

As a solutions provider, and depending on your business needs, we offer you extensive A-Z support in configuring your own 100 % customized CombiTac modular connector, including cable assembly if required.

This product catalog is dedicated to the CombiTac direct product line. To find out more about CombiTac uniq, please refer to the CombiTac uniq main catalog.

Further information concerning product portfolio, special features as well as exemplary videos can be found at [www.combitac.com](http://www.combitac.com)

# Content

<b>Page 6</b>	<b>The world of CombiTac</b> <ul style="list-style-type: none"> <li>• Plug into more possibilities</li> <li>• CombiTac Configurator</li> </ul>	<b>Page 26</b>	<b>Data modules</b> <ul style="list-style-type: none"> <li>• Module</li> <li>• Contacts</li> </ul>
<b>Page 8</b>	<b>CombiTac direct</b> <ul style="list-style-type: none"> <li>• The modular connector system</li> </ul>	<b>Page 30</b>	<b>Coaxial unit 6 GHz</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> </ul>
<b>Page 10</b>	<b>Ø 10 mm power up to 350 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 32</b>	<b>Coaxial unit 1,5 GHz</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> </ul>
<b>Page 12</b>	<b>Ø 7 mm power up to 120 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 34</b>	<b>Pneumatic 4 mm and 6 mm</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Compressed air couplings</li> </ul>
<b>Page 14</b>	<b>Ø 4 mm power up to 80 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 36</b>	<b>Single parts</b> <ul style="list-style-type: none"> <li>• Spacers</li> <li>• Frames</li> <li>• For details on  see page 73</li> </ul>
<b>Page 18</b>	<b>Ø 3 mm power up to 31 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 40</b>	<b>Housings</b> <ul style="list-style-type: none"> <li>• Aluminum housing IP65/67</li> <li>• Aluminum housing IP68</li> <li>• Plastic housing IP65</li> </ul>
<b>Page 20</b>	<b>Ø 1.5 mm Signal up to 14 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 65</b>	<b>Crimping pliers</b>
<b>Page 22</b>	<b>Ø 1 mm Signal up to 5 A</b> <ul style="list-style-type: none"> <li>• Contact carrier</li> <li>• Contacts</li> <li>• For details on  see page 73</li> </ul>	<b>Page 66</b>	<b>Appendix</b> <ul style="list-style-type: none"> <li>• Derating diagrams</li> <li>• Technical information</li> <li>• Safety notes</li> <li>• Safety situation for CombiTac connectors</li> <li>• Index</li> </ul>
<b>Page 24</b>	<b>Last Mate First Break module</b> <ul style="list-style-type: none"> <li>• Module</li> <li>• Last Mate First Break contacts</li> <li>• For details on  see page 73</li> </ul>		

# General information

## Changes/provisos

All data, illustrations, and drawings in the catalog have been carefully checked. They are in accordance with our experience to date, but no responsibility can be accepted for errors.

We also reserve the right to make modifications for design and safety reasons. When designing equipment incorporating our components, it is therefore advisable not to rely solely on the data in the catalog but to consult us to make sure this information is up to date. It would be our pleasure to advise you.

## Copyright

The use of this catalog for any other purpose, in whatever form, without our prior written consent is not permitted.

## Symbols



**The assembly instructions MA000 are available for this product**



**Surface Ag**



**Surface Au**

## Abbreviations

CTD	=	CombiTac direct
S	=	Socket
P	=	Pin
C	=	Carrier
C	=	Crimp termination
PE	=	Protective Earth
FP	=	Frame panel
FH	=	Frame housing
AWG	=	American Wire Gauge

## Aluminum DIN housings IP65/67

S	=	Side cable entry
T	=	Top cable entry
CH	=	Coupler hood
CHG	=	Coupler housing
PW	=	Protective wall
PC	=	Protective cover
SM	=	Surface mount
PM	=	Pedestal mount
PS	=	Park station
SSL	=	Space saving locking

## Aluminum housings IP68/69K, Plastic housings IP65

S	=	Side
G	=	Top
TG	=	Coupler hood
AG	=	Surface mount
SG	=	Pedestal mount

## RoHS Conformity

**European Directive 2011/65/EU (RoHS 2)**

**Commission Delegated Directive (EU) 2015/863 (RoHS 3)**

For further information please visit our website

[www.staubli.com/global/en/electrical-connectors/downloads/certificates/rohs-conformity.html](http://www.staubli.com/global/en/electrical-connectors/downloads/certificates/rohs-conformity.html)

THE WORLD OF COMBITAC

# Plug into more possibilities

Experience combined with quality and modularity leads to cost-efficient, and durable connection solutions. The modular connector system CombiTac can be easily configured online and adapted to meet the most

demanding requirements. Reliability when you need it. Flexibility, if you want it: The world of CombiTac's modular connector system meets your needs.

## CombiTac direct



Click & connect  
Most assembly-effective  
10,000 mating cycles

The latest generation of modular connectors for power, signal, and pneumatic connections up to 10,000 mating cycles. The new user-friendly, tool-free click-and-connect system allows you to assemble your modular connector system in the most time-saving way.

## CombiTac uniq



100 % customizable  
Highest performance  
100,000 mating cycles

Modular connectors for power, signal, data, pneumatic and fluid connections up to 100,000 mating cycles. Offers the highest possible performance and can be customized to meet exact technical and dimensional specifications.

# CombiTac Configurator


The CombiTac Configurator is a web application that enables you to put together your personalized CombiTac configuration

step by step on various end devices. It also allows you to receive a quotation for your selected CombiTac modular connector.



CombiTac Configurator

<https://configurator.combitac.com>



## COMBITAC DIREQT

# The modular connector system

### DIN coupler hoods

- 6 different sizes
- IP65/67, IP68/69K
- Aluminum or plastic
- Available in gray or white

### Frames

- 4 sizes for housing or panel mount
- Included in delivery

### CombiTac delivery status

- Contact carrier mounted on frames
- Contacts separately

### Possible connections

- Electrical signal
- Electrical power
- Protective earth (PE)
- Pneumatic

### Cable assembly

- On request

### DIN surface and pedestal mount housing

- 6 different sizes
- Aluminum or plastic
- Available in gray or white

### Mating cycles

- Panel mounted: up to 10,000
- Housing: up to 10,000 depending on type







Ø 10 MM POWER UP TO 350 A


# Contact carrier CTD-C10-1/...

1-pole contact carriers for 10 mm power contacts.


**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct insertion

**CTD-C10-1/S**



**CTD-C10-1/P**



Order No.	Type	Description
35.4101	CTD-C10-1/S	Socket carrier
35.4100	CTD-C10-1/P	Pin carrier
35.4109	CTD-RC10	Retaining clip (not included with carriers)

Technical data			
Number of poles	1		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>1)</sup>	Pollution degree 1: 1000 V	Pollution degree 2: 1000 V	Pollution degree 3: 500 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>1)</sup>	Overtoltage category I: 1000 V	Overtoltage category II: 1000 V	Overtoltage category III: 600 V
Rated voltage UL	600 V		
Degree of protection (socket and plug front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C		
Contact carrier material	PA		
Fire behavior	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	7		



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.



# Ø 10 mm contacts


10 mm power contacts up to 350 A.

**Features:**

- Tool-free insertion in carriers
- Quick removal of contacts through removal of holding clip
- MULTILAM Technology in sockets
- IP2X on socket and pin side
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004

CTD-S10/... AG

CTD-P10/... AG



Order No.	Type	Socket	Pin	Sur- face	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
35.0153 35.0553	CTD-S10/35 AG CTD-P10/35 IP2X AG	x	x		35	2	180	C
35.0152 35.0552	CTD-S10/50 AG CTD-P10/50 IP2X AG	x	x		50	1/0	225	C
35.0151 35.0551	CTD-S10/70 AG CTD-P10/70 IP2X AG	x	x		70	2/0	290	C
35.0150 35.0550	CTD-S10/95 AG CTD-P10/95 IP2X AG	x	x		95	4/0	350	C

**Accessories**

35.5656-04321	CTD-10-SRTU/43 <sup>3)</sup>	Shrink tubing 43 mm (not included in delivery)					
---------------	------------------------------	------------------------------------------------	--	--	--	--	--

**Technical data**

Nominal-Ø socket/pin	10 mm
Average sliding force	15 N
Connector resistance	< 40 µΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

<sup>3)</sup> Suitable for UL applications: UL-224 125 °C 600 V, file E48398

Ø 7 MM POWER UP TO 120 A



# Contact carrier CTD-C7-2/...

2-pole contact carriers for 7 mm power contacts.



**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion

**CTD-C7-2 /S**



**CTD-C7-2 /P**



Order No.	Type	Description
35.4071	CTD-C7-2/S	Socket carrier
35.4070	CTD-C7-2/P	Pin carrier
35.4079	CTD-RC7	Retaining clip (not included with carriers)

Technical data			
Number of poles	2		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>1)</sup>	Pollution degree 1: 1000 V	Pollution degree 2: 800 V	Pollution degree 3: 300 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>1)</sup>	Overvoltage category I: 1000 V	Overvoltage category II: 600 V	Overvoltage category III: 300 V
Rated voltage UL	600 V		
Degree of protection (socket and plug front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C		
Contact carrier material	PA		
Fire behavior	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	6		



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.



# Ø 7 mm contacts


7 mm power contacts up to 120 A.

**Features:**

- Tool-free insertion in carriers
- Quick removal of contacts through removal of holding clip
- IP2X on socket and pin side
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004
- MULTILAM Technology in sockets

**CTD-S7/... AG**

**CTD-P7/... AG**



Order No.	Type	Socket	Pin	Surface	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
35.0144 35.0544	CTD-S7/6 AG CTD-P7/6 IP2X AG	x	x		6	10	50	C
35.0143 35.0543	CTD-S7/10 AG CTD-P7/10 IP2X AG	x	x		10	8	70	C
35.0142 35.0542	CTD-S7/16 AG CTD-P7/16 IP2X AG	x	x		16	6	100	C
35.0141 35.0541	CTD-S7/25 AG CTD-P7/25 IP2X AG	x	x		25	4	120	C

Technical data	
Nominal-Ø socket/pin	7 mm
Average sliding force	17 N
Connector resistance	< 150 µΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

**Note:**

To guarantee IP2X protection when using 7 mm contacts in configurations which include a housing with side cable entry, you

must add a protective wall. This ensures protection of 7 mm contacts against damage in case housing falls on a hard surface.

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

Ø 4 MM POWER UP TO 80 A


# Contact carrier CTD-C-C4-2/...

2-pole contact carriers for 4 mm power and protective earth (PE) contacts.


**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion


**CTD-C-C4-2/S**




**CTD-C-C4-2/P**



**CTD-C-C4-2/S PE**



**CTD-C-C4-2/P PE**



**CTD-RC4**



Order No.	Type	Description
35.4043	CTD-C-C4-2/S	Socket carrier
35.4042	CTD-C-C4-2/P	Pin carrier
35.4045	CTD-C-C4-2/S PE	Socket carrier PE
35.4044	CTD-C-C4-2/P PE	Pin carrier PE
35.4049	CTD-RC4	Retaining clip (not included with carriers)

Technical data			
Number of poles	2		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>1)</sup>	Pollution degree 1: 1000 V	Pollution degree 2: 1000 V	Pollution degree 3: 600 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>1)</sup>	Overvoltage category I: 1000 V	Overvoltage category II: 1000 V	Overvoltage category III: 600 V
Rated voltage UL	600 V		
Degree of protection (socket and plug front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C		
Contact carrier material	PA		
Fire behavior	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	3		

### PE and Last Mate First Break (LMFB) Functionality

The plug contacts for 4 mm module are designed in **two variants**. Standard length (e.g., CTD-P4/4 IP2X AG ) and short (designated as “S”, e.g., CTD-P4/4-S IP2X AG). The LMFB functionality does not work when the short “S” male pins are used as power.

### Power + PE function

This function is achieved when PE is ensured via the standard length contact, in combination with the reduced length (S) contact for power transmission.

### For 2x power contacts only (or with the LMFB function)

Both the contacts with standard length for power transmission are used (or in combination with the usual LMFB module, if LMFB is needed).

We recommend using standard plug contacts as long as PE function is not required.

- The female contacts are the same.
- The carriers have to be selected according to functionality, with or without PE.



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

### Example for 4 mm contacts, with PE Function

Contact plug 1	Power contact CTD-P4/10-S IP2X AG (short)
Contact plug 2	PE contact CTD-P4/10 IP2X AG (inserted in PE labelled slot in carrier)
Contact socket 1 and 2	CTD-S4/4 AG
Socket carrier PE	CTD-C-C4-2/S PE
Pin carrier PE	CTD-C-C4-2/P PE

### Example for 4mm contacts power only (option possible with LMFB functionality)

Contact plug 1	CTD-P4/10 IP2X AG
Contact plug 2	CTD-P4/10 IP2X AG
Contact socket 1 and 2	CTD-S4/4 AG
Socket carrier	CTD-C-C4-2/S
Pin carrier	CTD-C-C4-2/P
Option LMFB	Use standard LMFB from CombiTac direct (1 mm) with above combination
Option power only	If only two power contacts (without LMFB) are needed, the two short contact plugs can also be used.

<sup>1)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.

# Ø 4 mm contacts

4 mm power contacts up to 80 A and protective earth (PE) contacts.

**Features:**


- Tool-free insertion in carriers
- Quick removal of contacts through removal of holding clip
- IP2X on socket and pin side
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004
- MULTILAM Technology in sockets

**Standard version**

**CTD-S4/... AG**



**CTD-P4/... IP2X AG**



**Special version with PE**


**CTD-S4/... AG**



**CTD-P4/... IP2X AG**



**CTD-P4/...-S IP2X AG**




**Further power modules in function with PE<sup>1)</sup>**

**CTD-S4/... AG**









**CTD-P4/...-S IP2X AG**



<sup>1)</sup> When more power contacts are needed with PE functionality, then add additional carriers with short contacts, CTD-P4/...-S IP2X AG.



Order No.	Type	Socket	Pin	Sur- face	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
<b>35.0138</b>	CTD-S4/4 AG	x			4	12	50	C 
<b>35.0538</b>	CTD-P4/4 IP2X AG		x					
<b>35.0548</b>	CTD-P4/4-S IP2X AG		x					
<b>35.0137</b>	CTD-S4/6 AG	x			6	10	55	C 
<b>35.0537</b>	CTD-P4/6 IP2X AG		x					
<b>35.0547</b>	CTD-P4/6-S IP2X AG		x					
<b>35.0136</b>	CTD-S4/10 AG	x			10	8	80	C 
<b>35.0536</b>	CTD-P4/10 IP2X AG		x					
<b>35.0546</b>	CTD-P4/10-S IP2X AG		x					

**Technical data**

Nominal-Ø socket/pin	4 mm
Average sliding force	9.5 N
Connector resistance	< 400 µΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

Ø 3 MM POWER UP TO 31 A

# Contact carrier CTD-C3-3/...



3-pole contact carriers for 3 mm power contacts or 2 × 3 mm power contact and protective earth (PE) contacts.

**Features:**




- Tool-free insertion in frames
- Quick removal with standard flat screw-driver

- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion
- PE version with marking



**CTD-C3-3/S**





**CTD-C3-2+PE/S**



**CTD-C3-3/P**



**CTD-C3-2+PE/P**



Order No.	Type	Description
35.4031	CTD-C3-3/S	Socket carrier
35.4030	CTD-C3-3/P	Pin carrier
35.4035	CTD-C3-2+PE/S	Socket carrier with ⊕
35.4034	CTD-C3-2+PE/P	Pin carrier with ⊕

Technical data			
Number of poles	3		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>1)</sup>	Pollution degree 1: 1000 V	Pollution degree 2: 600 V	Pollution degree 3: 250 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>1)</sup>	Overvoltage category I: 1000 V	Overvoltage category II: 600 V	Overvoltage category III: 300 V
Rated voltage UL	600 V		
Degree of protection (socket front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C		
Contact carrier material	PA		
Fire behavior	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	3		



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.



# ∅ 3 mm contacts

3 mm power contacts up to 31 A and protective earth (PE) contacts.

**Features:**

- Tool-free-insertion in carriers
- Quick removal with standard flat screw-driver
- Long pin PE version available
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004

CTD-S3/2,5-4 AU




CTD-P3/2,5-4 AU



CTD-S3/2,5-4 AU



CTD-P3/2,5-4/PE AU



Order No.	Type	Socket	Pin	Surface	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
35.0132	CTD-S3/2,5-4 AU	x			2.5	14	23	C
35.0532	CTD-P3/2,5-4 AU		x		4	12	31	C
35.0534	CTD-P3/2,5-4/PE AU		x		2.5 4	14 12	– <sup>3)</sup>	C

Technical data	
Nominal-∅ socket/pin	3 mm
Average sliding force	3 N
Connector resistance	< 1.1 mΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

<sup>3)</sup> Short circuit current 3s  
2.5 mm<sup>2</sup>: 157 A  
4 mm<sup>2</sup>: 252 A

Ø 1.5 MM SIGNAL UP TO 14 A


# Contact carrier CTD-C1,5-5/...

5-pole contact carriers for 1.5 mm signal contacts.


**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion

**CTD-C1,5-5/S**



**CTD-C1,5-5/P**



Order No.	Type	Description
35.4021	CTD-C1,5-5/S	Socket carrier
35.4020	CTD-C1,5-5/P	Pin carrier

Technical data			
Number of poles	5		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>1)</sup>	Pollution degree 1: 600 V	Pollution degree 2: 400 V	Pollution degree 3: 150 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>1)</sup>	Overvoltage category I: 600 V	Overvoltage category II: 300 V	Overvoltage category III: 150 V
Rated voltage UL	600 V		
Degree of protection (socket front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C		
Contact carrier material	PA		
Fire behavior	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	2		



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.



# Ø 1.5 mm contacts


1.5 mm signal contacts up to 14 A.

**Features:**

- Tool-free insertion in carriers
- Quick removal with standard flat screw-driver
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004

CTD-S1,5/0,75-1,5 AU

CTD-P1,5/0,75-1,5 AU



Order No.	Type	Socket	Pin	Surface	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
35.0120	CTD-S1,5/0,75-1,5 AU	×			0.75	18	8	C
35.0520	CTD-P1,5/0,75-1,5 AU		×		1.0	18	10	
					1.5	16	14	

**Technical data**

Nominal-Ø socket/pin	1.5 mm
Average sliding force	3 N
Connector resistance	< 2 mΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

Ø 1 MM SIGNAL UP TO 5 A


# Contact carrier CTD-C1...

7- or 21-pole contact carriers for 1 mm signal contacts.


**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion


**CTD-C1-7/S**




**CTD-C1-21/S**



**CTD-C1-7/P**



**CTD-C1-21/P**



Order No.	Type	Description
35.4011	CTD-C1-7/S	Socket carrier
35.4010	CTD-C1-7/P	Pin carrier
35.4013	CTD-C1-21/S <sup>1)</sup>	Socket carrier
35.4012	CTD-C1-21/P <sup>1)</sup>	Pin carrier

Technical data			
Number of poles	7 or 21		
Max. voltage RMS pin-to-pin and pin-to-GND <sup>2)</sup>	Pollution degree 1:	Pollution degree 2:	Pollution degree 3:
	600 V	400 V	150 V
Max voltage Line-to-Neutral for pins energized directly from mains supply <sup>2)</sup>	Overvoltage category I:	Overvoltage category II:	Overvoltage category III:
	600 V	300 V	150 V
Rated voltage UL	600 V		
Degree of protection (socket front)	IP2X		
Clearances and creepage distance	IEC 60664-1:2020 and UL 1977		
Limiting temperature (IEC 61984:2008), upper lower	+125 °C		
	-40 °C		
Contact carrier material	PA		
Fire behaviour	EN45545-2:2015 (HL2 R22)		
Grid unit in frame	2 or 4		



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> The 21-pole contact carrier can be used also for LMFB (last mate first break) option, on request.

<sup>2)</sup> Voltage levels according to IEC 61984:2008 and IEC 60664-1:2020.



# ∅ 1 mm contacts

1 mm signal contacts up to 5 A.

**Features:**

- Tool-free insertion in carriers
- Quick removal with standard flat screw-driver
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004



CTD-S1/... AU





CTD-P1/... AU



CTD-C1-7/...



CTD-C1-21/...



Order No.	Type	Socket	Pin	Sur- face	Conductor cross section		Rated current <sup>1), 2)</sup> A	Type of termination
					mm <sup>2</sup>	AWG		
35.0110	CTD-S1/0,14-0,25 AU	x			0.14	26	2	C
35.0510	CTD-P1/0,14-0,25 AU		x		0.25	24	3	
35.0111	CTD-S1/0,25-0,75 AU	x			0.25	24	3	C
35.0511	CTD-P1/0,25-0,75 AU		x		0.5	20	4	
35.0511	CTD-P1/0,25-0,75 AU		x		0.75	18	5	

**Technical data**

Nominal-∅ socket/pin	1 mm
Average sliding force	1 N
Connector resistance	< 3 mΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

<sup>1)</sup> IEC rated current for fully assembled frames size 4. Wires unbundled, free in air. See pages 66 – 69 for corresponding diagrams for multiple, bundled wires.

<sup>2)</sup> Current rating for AWG cables can vary depending on cable manufacturer.

# LAST MATE FIRST BREAK MODULE

## Module CTD-LMFB-...

Last Mate First Break (LMFB) contacts are intended for monitoring purposes, and show whether a CombiTac is fully connected or not. Each CombiTac LMFB module consists of two LMFB contacts.


Suitable for panel mount and housing applications.

**Note:**


- Size 1 frames require one LMFB module, which can be placed in any position in the frame.
- Size 2 – 4 frames require two LMFB modules which are positioned at the

edge positions of the frame. Empty carrier slots (position 2 – 6) may be used with 1 mm signal contacts (page 23).

CTD-LMFB-S...




CTD-LMFB-P...



Order No.	Type	Description
35.4017	CTD-LMFB-S/0,14-0,25	Socket module
35.4016	CTD-LMFB-P/0,14-0,25	Pin module
35.4019	CTD-LMFB-S/0,25-0,75	Socket module
35.4018	CTD-LMFB-P/0,25-0,75	Pin module

Technical data	
Number of poles	7 (slots 1 and 7 for LMFB contacts)
Limiting temperature (IEC 61984:2008), upper	+125 °C
lower	-40 °C
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Grid unit in frame	2



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)





# Last Mate First Break contacts CTD-LMFB...


To be used with contact carrier CTD-C1-7/... for monitoring the connection status of electrical contacts Ø 3 mm – Ø 10 mm.

**Features:**

- Tool-free insertion in carriers
- Quick removal with standard flat screw-driver
- Resistance to shock and vibrations
- Crimp termination (C) for Cu conductors (class 5 and 6) according to IEC 60228:2004

CTD-LMFB-S...

CTD-LMFB-P...



Order No.	Type	Socket	Pin	Surface	Conductor cross section		Type of termination
					mm <sup>2</sup>	AWG	
35.0112	CTD-LMFB-S1/0,14-0,25 AU	×			0,14	26	C
35.0512	CTD-LMFB-P1/0,14-0,25 AU		×		0,25	24	
35.0113	CTD-LMFB-S1/0,25-0,75 AU	×			0,25	24	C
35.0513	CTD-LMFB-P1/0,25-0,75 AU		×		0,5	20	
					0,75	18	

Technical data	
Rated voltage/system voltage	U <sub>DC</sub> 29,5 V
Max. signal current	100 mA
Nominal-Ø socket/pin	1 mm
Average sliding force	1 N
Connector resistance	< 3 mΩ
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 Category 1B

**Note:**

When using carrier positions 2 – 6 with Ø 1 mm Signal contacts, the technical specifications of carriers and contacts of pages 22 – 23 apply.

## DATA MODULES

# 1 Gbit module CTD-NET...

This data module is part of the CombiTac direct rectangular modular connector system.


1 Gbit crimp data modules are used for Ethernet communication up to 1 Gbit/s (CAT5e).

### Features:


- 10,000 mating cycles
- 100 Mbit or 1 Gbit depending on cable type
- Tool-free insertion in frames

- Quick removal of carriers with standard flat screwdriver
- Applications: data communication, machine-to-machine communication (M2M), real time facility data sharing

### CTD-NET-1/S



### CTD-NET-1/P



### CTD-RC-UDM-NET



Order No.	Type	Number of contacts
35.4151	CTD-NET-1/S	Contacts not included in carrier.
35.4150	CTD-NET-1/P	Selection of number of contacts and contact arrangement depending on application (see next page).
35.4143	CTD-RC-UDM-NET	Retaining clip (included in carrier)

Technical data	
Data transmission	Up to 1 Gbit CAT5e Ethernet IEEE 802.3 <sup>1)</sup> , Profibus, Profinet, Interbus, CAN-BUS, USB 2.0, PoE <sup>2)</sup>
Mating cycles	10,000
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C
Contact carrier material Insulation	PA PEEK
Fire behaviour	EN45545-2:2015 (HL2 R22)
Grid unit in frame	5



Assembly instructions MA417-1

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Further technical specifications:  
[www.staubli.com/electrical](http://www.staubli.com/electrical) > Downloads > Technical Info > Industry > Data connectors.

<sup>2)</sup> According to the IEC 60512-99-001 (100 mating cycles)

# Contacts for data transfer CTD-NET...

For contact carrier CTD-NET... Sockets fitted with MULTILAM.



**Features:**

- Tool-free insertion in frames
- Quick removal of contacts with extraction tool
- Crimp termination (C) to a Cu conductor (class 5 and 6)

CT-NET-B...



CT-NET-S...



Order No.	Type	Socket	Pin	Surface	Conductor cross section		Rated current	Type of termination
					mm <sup>2</sup>	AWG		
33.0148	CT-NET-BP1 ET/0,14-0,75 AU	x			0.14	26	1	C
					0.25	24	2	
33.0548	CT-NET-SP1/0,14-0,75 AU		x		0.34	22	3	
					0.5 <sup>1)</sup>	20	3	
					0.75 <sup>1)</sup>	18	5	
33.9589	CT-NET-BS <sup>2)</sup>	Blind plug						
33.3048	CT-NET-AWZ	Extraction tool						


Technical data	
Nominal-Ø socket/pin	Ø 1 mm
Average sliding force per connection (8 pins and shield)	10.5 N
Connector resistance	1.8 mΩ
Max. outer diameter per wire	2.3 mm
Maximum outer diameter over the whole cable with special nut CT-NET-MU.PFB; Order No. 13009834 and pliers CT-NET-Z-PFB; Order No. 13009832	7.5 mm 8.5 mm

**Contact arrangement of the contact carrier**


Left: socket side; right: pin side  
(Viewed from the termination side)

**CAT5**


**Ethernet/Profinet**



**Interbus**



**Profibus**




<sup>1)</sup> Maximal four wires per connector

<sup>2)</sup> Unused contact slots can be closed with blind plugs.

**CAT5e**

**Ethernet/Profinet**



Assembly instructions MA417-1

www.staubli.com/electrical


# 1 Gbit module CTD-RJ45...

1 Gbit RJ45 data modules are used for Ethernet communication up to 1 Gbit/s (CAT5). Suitable network cables with a RJ45 connectors can be directly connected to the module. The 1 Gbit RJ45 module is delivered completely assembled.


**Features:**

- 10,000 mating cycles
- 100 Mbit or 1 Gbit depending on cable type
- Resistance to shock and vibrations
- Quick removal of carriers with standard flat screwdriver
- Applications: data communication, machine-to-machine communication (M2M), real time facility data sharing


**CTD-RJ45-1/S**




View from rear view



**CT-RJ45-1/P**



View from rear view



**CTD-RC-UDM-RJ45**



Order No.	Type	
35.4161	CTD-RJ45-1/S	Complete RJ45 carrier with connector Socket Side
35.4160	CTD-RJ45-1/P	Complete RJ45 carrier with connector Pin Side

**Individual part**

35.4142	CTD-RC-UDM-RJ45	Retaining clip (included in carrier)
---------	-----------------	--------------------------------------

Technical data	
Data transmission	Up to 1 Gbit CAT5e Ethernet IEEE 802.3 <sup>1)</sup> , USB 2.0
Mating cycles	10,000
Average sliding force	9.5 N
Limiting temperature (IEC 61984:2008), upper lower	+125 °C -40 °C
Contact carrier material	PA
Insulation	PEEK
Fire behaviour	EN45545-2:2015 (HL2 R22)
Vibrations and shock	IEC 61373:2010 Category 1B
Grid unit in frame	5



**Assembly instructions MA417-1**

[www.staubli.com/electrical](http://www.staubli.com/electrical)

<sup>1)</sup> Further technical specifications:  
[www.staubli.com/electrical](http://www.staubli.com/electrical) > Downloads > Technical Info >  
 Industry > Data connectors.

## COAXIAL UNIT 6 GHZ

# Contact carrier

The Coaxial units are used for data as well as digital audio and video transmission.

Two types of termination are possible, crimp and SMA.

A crimp version is available for RG316/U cable types which is also suitable for RG174 and RG188 cable.



An SMA termination version allows the connection of various cable types up to 6 GHz levels.

### Features:

- Suitable for various 50 Ω RG cable types up to 6 GHz (depending on RG cable type)
- Crimp for RG58 cables up to 2.4 GHz
- Crimp for RG316/U, RG174, RG188 cables up to 2.4 GHz
- SMA up to 6 GHz
- 10,000 mating cycles

- Resistance to shock and vibrations
- Tool-free insertion in frames
- Quick removal of carriers with standard flat screwdriver
- Applications: data transmission, digital audio and video, HF measurement, radio communication.

### CTD-CUDM-SH



### CTD-RC-UDM-COAX



Order No.	Type	Designation
35.4139	CTD-CUDM-SH	One pole coax carrier; Retaining clip CTD-RC-UDM-COAX not included

### Individual part

35.4141	CTD-RC-UDM-COAX	Retaining clip for coaxial connectors listed on page 31.
---------	-----------------	----------------------------------------------------------

Technical data	
Number of poles	1
For connectors	Coaxial crimp and SMA
Limiting temperature (IEC 61984:2008), upper	+90 °C
lower	-40 °C
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Grid unit in frame	5

# Coaxial connectors

For contact carrier CTD-CUDM.


**Type of termination:**

- Crimp termination (C)
- SMA Termination (SMA)

**CT-B-COAX-RG316/U**




**CT-S-COAX-RG316/U**



**CT-B-COAX-SMA**



**CT-S-COAX-SMA**



Order No.	Type	Socket	Pin	Suitable for cable types	Type of termination
<b>33.0230</b> <b>33.0630</b>	CT-B-COAX-RG316/U CT-S-COAX-RG316/U	×	×	RG316/U, RG174, RG188	C
<b>33.0231</b> <b>33.0631</b>	CT-B-COAX-RG58 CT-S-COAX-RG58	×	×	RG58	C
<b>33.0250</b> <b>33.0750</b>	CT-B-COAX-SMA CT-S-COAX-SMA	×	×	RG58, RG316/U, RG174, RG188, other 50 Ω RG cable types up to 6 GHz	SMA

**Technical data**

Average sliding force per contact	8 N
Surface, Inner conductor	Au
Shield	Ag
Max. frequency	Crimp: 2.4 GHz      SMA: 6 GHz
Voltage standing wave ratio (VSWR)	Crimp: 1.4 at 2.4 GHz      SMA: 1.3 at 6 GHz
Pollution degree/overvoltage category	2/CAT II
Rated voltage IEC 60664-1	300 V
Rated voltage UL	250 V
Rated current	250 mA
Impedance	50 Ω
Mating cycles	10,000
Vibrations and shock	IEC 61373:2010 category 1B
Degree of protection (socket front)	IP2X



**Assembly instructions MA417-1**

[www.staubli.com/electrical](http://www.staubli.com/electrical)

**COAXIAL UNIT 1.5 GHZ**

# Contact carrier

This coaxial unit is used for data as well as digital audio and video transmission.



This coaxial module is designed for RG58 type cables for applications up to 1.5 GHz.

**Features:**

- Suitable for various 50 Ω RG cable types
- Crimp for RG58 cables up to 1.5 GHz
- Up to 5000 mating cycles
- Resistance to shock and vibrations
- Tool-free insertion in frames

- Quick removal of carriers with standard flat screwdriver
- Applications: data transmission, digital audio and video, HF measurement, radio communication.

**CTD-CUDM-SH**



**CTD-RC-UDM-RJ45**



Order No.	Type	Designation
35.4139	CTD-CUDM-SH	One pole coax carrier; Retaining clip CTD-RC-UDM-RJ45 not included

**Individual part**

35.4142	CTD-RC-UDM-RJ45	Retaining clip for coaxial connectors listed on page 33.
---------	-----------------	----------------------------------------------------------

Technical data	
Number of poles	1
For connectors	Coaxial crimp
Limiting temperature (IEC 61984:2008), upper	+90 °C
lower	-40 °C
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Grid unit in frame	5



# Coaxial connectors

For contact carrier CTD-CUDM-SH.


**Type of termination:**



- Crimp termination (C)

**CTD-S/COAX58**



**CTD-P/COAX58**



Order No.	Type	Socket	Pin	Suitable for cable types	Type of termination
35.0158	CTD-S/COAX58	x		RG58	C 
35.0558	CTD-P/COAX58		x	RG58	C 

**Technical data**

Average sliding force per contact	20 N	
Surface, Inner conductor	Au	
Shield	Ni	
Max. frequency	1.5 GHz	
Voltage standing wave ratio (VSWR)	≤1.25 at f < 1.5 GHz	
Pollution degree/overvoltage category	2/CAT II	
Rated voltage acc. to IEC 61010	300 V	
Rated current	1 A	
Impedance	50 Ω	
Mating cycles	acc. to IEC 61984: 5000	acc. to IEC 61169-8: 1000
Degree of protection (socket front)	IP2X	



Assembly instructions MA417-1

[www.staubli.com/electrical](http://www.staubli.com/electrical)

PNEUMATIC 4 MM AND 6 MM


# Contact carrier CTD-CP-2/...

2-pole contact carriers for pneumatic couplings.


**Features:**

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations
- Coded carriers for correct polarity insertion

**CTD-CP-2/S**



**CTD-CP-2/P**



Order No.	Type	Description
35.4121	CTD-CP-2/S	Socket carrier
35.4120	CTD-CP-2/P	Pin carrier

Technical data	
Number of poles	2
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Grid unit in frame	6



Assembly instructions MA417

[www.staubli.com/electrical](http://www.staubli.com/electrical)

# Compressed air couplings

4 mm and 6 mm pneumatic couplings.


**Features:**

- With or without shut-off valve

CT-B...-RCT03/...



CT-S...-RCT03/...



Order No.	Type	Socket	Plug	Outer-Ø D of the tube		A	Shut-off		Press ring color
				mm	"		without	with	
							←	●	
33.0180	CT-B-RCT03/4	x		4	(5/32)	14	x		●
33.0181	CT-BV-RCT03/4	x		4	(5/32)	14		x	●
33.0580	CT-S-RCT03/4		x	4	(5/32)	7	x		●
33.0182	CT-B-RCT03/6 <sup>1)</sup>	x		6		17	x		●
33.0183	CT-BV-RCT03/6 <sup>1)</sup>	x		6		17		x	●
33.0582	CT-S-RCT03/6 <sup>1)</sup>		x	6		11.5	x		●

**Technical data**

Nominal bore (mm)	03
Max. working pressure (bar)	15
Min. working pressure (mbar)	14
Operating temperatures	-15 °C ... +90 °C
Sealing materials	NBR
Mating cycles	10,000

<sup>1)</sup> For flow, head loss diagrams, and sliding forces, see page 70.

## SINGLE PARTS


# Spacers

Dips for filling up empty frame spaces.

### Features:

- Tool-free insertion in frames
- Quick removal with standard flat screw-driver
- Railway-compliant material
- Resistance to shock and vibrations

CTD-DIP3,5



Order No.	Type
35.4135	CTD-DIP3,5

Technical data	
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Vibrations and shock	IEC 61373:2010 Category 1B
Grid unit in frame	1

# Frames

4 types of frames for housings or panel mount applications.

**Features:**

- Coded frames for correct polarity during connection (male/female)
- Coded frames for correct polarity carrier insertion

- Grounding connection up to 6 mm<sup>2</sup> earth conductors  
Type of termination: Flat connector termination 6.3 mm x 0.8 mm
- Numbered frames for position identification
- Float mounting panel mount frames for +/- 1 mm misalignment absorption

**Panel mounted**

**CTD-FP.../S**



**Housing assembly**

**CTD-FH.../S**




Panel mounted		Housing assembly		Description	No. of grids units in frame
Order No.	Type	Order No.	Type		
35.4291	CTD-FP1/S	35.4221	CTD-FH1/S	Assembled frame socket side	7
35.4281	CTD-FP1/P	35.4201	CTD-FH1/P	Assembled frame plug side	
35.4292	CTD-FP2/S	35.4222	CTD-FH2/S	Assembled frame socket side	11
35.4282	CTD-FP2/P	35.4202	CTD-FH2/P	Assembled frame plug side	
35.4293	CTD-FP3/S	35.4223	CTD-FH3/S	Assembled frame socket side	17
35.4283	CTD-FP3/P	35.4203	CTD-FH3/P	Assembled frame plug side	
35.4294	CTD-FP4/S	35.4224	CTD-FH4/S	Assembled frame socket side	24
35.4284	CTD-FP4/P	35.4204	CTD-FH4/P	Assembled frame plug side	

Technical data	
Contact carrier material	PA
Fire behavior	EN45545-2:2015 (HL2 R22)
Vibrations and shock	IEC 61373:2010 Category 1B

## CALCULATION OF INSTALLATION DIMENSIONS


# Drilling plan

for frame panel mounting



Size	Frame size (mm)			
	1	2	3	4
L1	44	57	78	104
L2	63	76	97	123

for frame housing assembly




Size	Frame size (mm)			
	1	2	3	4
A	44	57	78	104
B	40	53	74	100
C	38	51	72	98


PANEL MOUNTING

# Panel mounting


## Max. permissible mounting offset



## Max. permissible mounting angular misalignment during mating



## Max. permissible distance between the contact carriers when mated



Contacts	Sizes X
	max. mm
CTD 10	6
CTD 7	6
CTD 3	6
CTD 1,5	3
CTD 1	2
RCT03	1.5

## ALUMINUM HOUSINGS INTRODUCTION

# Standard DIN housings

Aluminum DIN housings are designed to serve general industrial, healthcare and railway applications. Standard and Space Saving locking mechanisms available.

Available in grey and white color depending on size. Other colors available upon request.

### Features depending on type (see table page 41 for details):

- Up to 10,000 mating cycles
- IP65 and IP67 in mated condition
- 6 coding possibilities
- Quick and easy replacement of sealing
- Resistance to shock and vibrations
- IP2X during connecting/disconnecting process when using protective walls
- Ergonomic locking mechanism
- Space saving locking available to save space when placing a high number of housings next to each other

### Benefits:

- Minimum service costs
- Added user safety
- Low maintenance costs
- Reliable solution
- Easy handling

## Coupler hoods/Surface and pedestal mount housings




### Coupler hoods

Can be used with a surface or pedestal mount housing. Available with side or top cable entry, with or without protective wall.

### Surface and pedestal mount housings

Both types are used with coupler hoods. The choice of mount housing depends on the cable entry type. Available with or without protective wall or cover.

## Coupler hoods and surface housings with space saving locking



### Coupler hoods


Can be used with a surface mount housing. Available with side or top cable entry.

### Surface mount housings

Used with coupler hoods.



## Accessories



### Park stations

- For parking coupler hoods when not in use

### Replacement seals (depending on type)

- Available upon request

## Technical data DIN housings

Technical data	
Housing material	Aluminum
Seal material	NBR
Locking mechanism material	Stainless steel
Vibrations and shock	IEC 61373:2010 Category 1B

## Comparison chart of the different housings

Size	IP65	IP67	Mating cycles	Color	Temperature range	Vibrations and shock	Replaceable seal
						IEC 62847:2016	
1	x		5,000	Grey RAL9006	-40 °C to +90 °C		
2	x	x	10,000	Grey RAL7012 White RAL9003	-40 °C to +125 °C short-term operation -40 °C to +90 °C continuous operation	x	x
3	x	x	10,000	Grey RAL7012 White RAL9003	-40 °C to +125 °C short-term operation -40 °C to +90 °C continuous operation	x	x
4	x	x	10,000	Grey RAL7012 White RAL9003	-40 °C to +125 °C short-term operation -40 °C to +90 °C continuous operation	x	x
5	x		5,000	Grey RAL9006	-40 °C to +90 °C		
6	x		5,000	Grey RAL9006	-40 °C to +90 °C		

<sup>1)</sup> Follow maintenance instructions according to MA213


## ALUMINUM HOUSING IP65/67

# Coupler hood

Coupler hoods can be combined with surface or pedestal mount housing. Available with side or top cable entry.

### Note for sizes 2, 3, 4:

For white housing please add the color code number 29, e.g. 33.2362-29. Other colors available upon request.




Size	Order No.	Type	IP65	IP67	Cable entry		Sizes (mm)				Standard color
					Side	Top	A1	A2	A3	A6	
1	33.1551	CT-CH1-S	x		x		60	43	72	M32	■
	33.1571	CT-CH1-T	x			x					
2	33.2402	CT-CH2-S	x	x	x		73.8	43.9	70	M32	■ 29
	33.2362	CT-CH2-T	x	x		x					
3	33.2403	CT-CH3-S	x	x	x		93.8	43.9	76	M32	■ 29
	33.2363	CT-CH3-T	x	x		x					
4	33.2404	CT-CH4-S	x	x	x		120.8	43.9	78	M32	■ 29
	33.2364	CT-CH4-T	x	x		x					
5	33.0365	CT-CH5-S	x		x		95	82.5	79	M40	■
	33.0355	CT-CH5-T	x			x					
6	33.0366	CT-CH6-S	x		x		131	89	96	M50	■
	33.0356	CT-CH6-T	x			x					


# Coupler housing

Coupler housings can be combined with coupler hoods. Available with top cable entry.

## CT-CHG...-T



## CT-CHG...-T/PW



Size	Order No.	Type	IP65	IP67	Cable entry	Protective wall	Sizes (mm)					Standard color
							A1	A2	A3	A4	A6	
1	33.1501	CT-CHG1-T	x		Top		60	43	75	20	M32	
2	33.5082	CT-CHG2-T	x	x	x		73	43	74	35	M32	29
	33.5092	CT-CHG2-T/PW	x	x		x						
3	33.5083	CT-CHG3-T	x	x	x		93.5	43	80	35	M32	29
	33.5093	CT-CHG3-T/PW	x	x		x						
4	33.5084	CT-CHG4-T	x	x	x		120	43	82	35	M32	29
	33.5094	CT-CHG4-T/PW	x	x		x						
5	33.0415	CT-CHG5-T	x		x		95	82.5	82.5	33	M40	



Assembly instructions MA213

[www.staubli.com/electrical](http://www.staubli.com/electrical)


# Coupler hood with protective wall, IP2X

Coupler hoods with protective walls offer additional damage protection to contacts along with IP2X protection during the connecting/disconnecting process. Protective walls are in black.


**Note for sizes 2, 3, 4:**






For white housing please add the color code number 29, e.g. 33.2362-**29**. Other colors available upon request.

**CT-CH...PW**








**CT-CH...PW-PC**



Size	Order No.	Type	IP65	IP67	Cable entry		Sizes (mm)				Standard color
					Side	Top	A1	A2	A3	A6	
2	33.2952	CT-CH2-S/PW	x	x	x		78.5	51.5	86.5	M32	 29
	33.2912	CT-CH2-T/PW	x	x		x					
3	33.2953	CT-CH3-S/PW	x	x	x		99	51.5	92.5	M32	 29
	33.2913	CT-CH3-T/PW	x	x		x					
4	33.2954	CT-CH4-S/PW	x	x	x		125.2	51.5	94.5	M32	 29
	33.2914	CT-CH4-T/PW	x	x		x					
5	33.3255	CT-CH5-S/PW	x		x		101	91	95.5	M40	
	33.3275	CT-CH5-T/PW	x			x					
6	33.3256	CT-CH6-S/PW	x		x		136	98.5	121	M50	
	33.3276	CT-CH6-T/PW	x			x					

for use with housings that include protective covers

2	33.2972	CT-CH2-S/PW-PC	x	x	x		78.5	51.5	86.5	M32	 29
	33.2932	CT-CH2-T/PW-PC	x	x		x					
3	33.2973	CT-CH3-S/PW-PC	x	x	x		99	51.5	92.5	M32	 29
	33.2933	CT-CH3-T/PW-PC	x	x		x					
4	33.2974	CT-CH4-S/PW-PC	x	x	x		125.2	51.5	94.5	M32	 29
	33.2934	CT-CH4-T/PW-PC	x	x		x					
5	33.3295	CT-CH5-S/PW-PC	x		x		101	91	95.5	M40	
	33.3225	CT-CH5-T/PW-PC	x			x					
6	33.3296	CT-CH6-S/PW-PC	x		x		136	98.5	121	M50	
	33.3226	CT-CH6-T/PW-PC	x			x					

# Surface mount housing


Surface mount housings are used for bottom cable entry. They are combined with coupler hoods and are available with or without protective wall or cover. Protective walls are in black.

Coupler hoods with protective walls of fer additional damage protection to contacts along with IP2X protection during the connecting/disconnecting process.


**Note for sizes 2, 3, 4:**

For white housing please add the color code number 29, e.g. 33.2362-**29**. Other colors available upon request.


**CT-SM...**









**CT-SM...PW**



**CT-SM...PC**



Size	Order No.	Type	IP65	IP67	Protective cover	Protective wall	Sizes (mm)					Standard color	
							A1	A2	A3	A4	A5		
<b>1</b>	<b>33.1561</b>	CT-SM1	x				82	43	29	20	–		
	<b>33.1591</b>	CT-SM1-PC	x		x	26.5							
<b>2</b>	<b>33.2302</b>	CT-SM2	x	x			94	44.9	28.5	32.9	–		
	<b>33.2852</b>	CT-SM2/PW	x	x		x							29.6
	<b>33.2332</b>	CT-SM2-PC	x	x	x								29.8
<b>3</b>	<b>33.2303</b>	CT-SM3	x	x			114	44.9	28.5	32.9	–		
	<b>33.2853</b>	CT-SM3/PW	x	x		x							29.6
	<b>33.2333</b>	CT-SM3-PC	x	x	x								29.8
<b>4</b>	<b>33.2304</b>	CT-SM4	x	x			141	44.9	28.5	32.9	–		
	<b>33.2854</b>	CT-SM4/PW	x	x		x							29.6
	<b>33.2334</b>	CT-SM4-PC	x	x	x								29.8
<b>5</b>	<b>33.0375</b>	CT-SM5	x				124	90	36	27	–		
	<b>33.3235</b>	CT-SM5/PW	x			x							26.4
	<b>33.0385</b>	CT-SM5-PC	x		x								22
<b>6</b>	<b>33.0376</b>	CT-SM6	x				165	90	38.5	50	–		
	<b>33.0386</b>	CT-SM6-PC	x		x	25							

# Pedestal mount housing


Pedestal mount housings are used for left and/or right side cable entry. They are combined with coupler hoods and are available with or without protective wall or cover. Protective walls are black.

Pedestal mount with protective walls of-fer additional damage protection to con-tacts along with IP2X protection during the connecting/disconnecting process.


**Note for sizes 2, 3, 4:**

For white housing please add the color code number 29, e.g. 33.2362-29. Other colors available upon request.


**CT-PM...**








**CT-PM...PW**



**CT-PM...PC**





Size	Order No.	Type	IP65	IP67	Protective cover	Protective wall	Sizes (mm)						Standard color	
							A1	A2	A3	A4	A5	A6		
1	33.1541	CT-PM1	x				82	54.5	74	13.5	-	20	M32	
	33.1581	CT-PM1-PC	x		x									
2	33.2462	CT-PM2	x	x			94	57	74	26.9	-	-	M32	 29
	33.2872	CT-PM2/PW	x	x		x			86.9					
	33.2702	CT-PM2-PC	x	x	x				74					
3	33.2463	CT-PM3	x	x			117	57	77	26.9	-	-	M32	 29
	33.2873	CT-PM3/PW	x	x		x			90					
	33.2703	CT-PM3-PC	x	x	x				77					
4	33.2464	CT-PM4	x	x			144	57	79	26.9	-	-	M32	 29
	33.2874	CT-PM4/PW	x	x		x			92					
	33.2704	CT-PM4-PC	x	x	x				79					
5	33.1025	CT-PM5	x				126	92.5	78.5	33	-	-	M32	
	33.2085	CT-PM5/PW	x			x			92.8					
	33.1035	CT-PM5-PC	x		x				78.5					
6	33.0396	CT-PM6	x				140	120	98.5	37	-	10	M40	
	33.0406	CT-PM6-PC	x		x									


# Park stations

Used for parking coupler hoods when they are not connected to mount housings.


**Note for sizes 2, 3, 4:**

For white housing please add the color code number 29, e.g. 35.1742-29. Other colors available upon request.


**CTD-PS...SM/P**



**CTD-PS...SM/S**




**CTD-PS...PC-SM/S**



Size	Order No.	Type	IP65	IP67	Pin end pieces	Socket end pieces	Protective cover	Sizes (mm)					Standard color
								A1	A2	A3	A4	A5	
1	35.1741	CTD-PS1-SM/P	x		x			82	43	29	21		
	35.1731	CTD-PS1-SM/S	x			x							
	35.1721	CTD-PS1/PC-SM/S	x			x	x						
2	35.1742	CTD-PS2-SM/P	x	x	x			94	44.9	28.5	32.9	29.8	29
	35.1732	CTD-PS2-SM/S	x	x		x							
	35.1722	CTD-PS2/PC-SM/S	x	x		x	x						
3	35.1743	CTD-PS3-SM/P	x	x	x			114	44.9	28.5	32.9	29.8	29
	35.1733	CTD-PS3-SM/S	x	x		x							
	35.1723	CTD-PS3/PC-SM/S	x	x		x	x						
4	35.1744	CTD-PS4-SM/P	x	x	x			141	44.9	28.5	32.9	29.8	29
	35.1734	CTD-PS4-SM/S	x	x		x							
	35.1724	CTD-PS4/PC-SM/S	x	x		x	x						
5	35.1745	CTD-PS5-SM/P	x		x			124	84	36	33	22	
	35.1735	CTD-PS5-SM/S	x			x							
	35.1725	CTD-PS5/PC-SM/S	x			x	x						
6	35.1746	CTD-PS6-SM/P	x		x			165	90	38.5	50	25	
	35.1736	CTD-PS6-SM/S	x			x							
	35.1726	CTD-PS6/PC-SM/S	x			x	x						

## Replacement seals

Replacement housing seals made of NBR can be reordered.



CT-DDI-SM...



CT-PDI-SM...

Size	Order No.	Type	Description
2	33.2782	CT-DDI-SM2	Upper seal
3	33.2783	CT-DDI-SM3	
4	33.2784	CT-DDI-SM4	
2	33.2792	CT-PDI-SM2	Lower seal
3	33.2793	CT-PDI-SM3	
4	33.2794	CT-PDI-SM4	

# Selection of special DIN housings for CombiTac Ø 10 mm contacts

**Step 1:** Select the number of Ø 10 mm poles of your CombiTac connector (e.g. 2 x Ø 10 mm pole)

**Step 2:** Select the outer insulation diameter of your cable (e.g. 17 mm)

**Step 3:** Select the appropriate cable gland (e.g. order No. 33.4126 or 33.4122)

**Step 4:** Select a suitable DIN housing (e.g. size 3, order No. 33.2713)

1 Number of poles	2 For Ø cable mm	3 Cable gland				4 Suitable housing							
		Size M	Order No.	Type	Wrench size max. mm	Size	Order No.	Type	Position of cable glands				
1	14 – 17	32	<b>33.4123</b>	CT-K-VSH M32x14-17 MS	36	2	<b>33.2362</b>	CT-CH2-T					
	17 – 21		<b>33.4124</b>	CT-K-VSH M32x17-21 MS									
	21 – 25		<b>33.4125</b>	CT-K-VSH M32x21-25,5 MS									
2	9.5 – 12.5	25	<b>33.4120</b>	CT-K-VSH M25x9,5-12,5 MS	30	3	<b>33.2713</b>	CT-CH3-T/2xM25					
	10 – 17		<b>33.4126</b>	CT-K-VSH M25x10-17 MS	28								
	16 – 20.5		<b>33.4122</b>	CT-K-VSH M25x16-20,5 MS	30								
	14 – 17	32	<b>33.4123</b>	CT-K-VSH M32x14-17 MS	36					4	<b>35.1204</b>	CT-CH4-T/2xM32	
	17 – 21		<b>33.4124</b>	CT-K-VSH M32x17-21 MS									
	21 – 25		<b>33.4125</b>	CT-K-VSH M32x21-25,5 MS									
3	9.5 – 12.5	25	<b>33.4120</b>	CT-K-VSH M25x9,5-12,5 MS	30	4	<b>33.2744</b>	CT-CH4-T/3xM25					
	10 – 17		<b>33.4126</b>	CT-K-VSH M25x10-17 MS	28								
	16 – 20.5		<b>33.4122</b>	CT-K-VSH M25x16-20,5 MS	30								
	14 – 17	32	<b>33.4123</b>	CT-K-VSH M32x14-17 MS	36					6	<b>33.3196</b>	CT-CH6-T/3xM32	
	17 – 21		<b>33.4124</b>	CT-K-VSH M32x17-21 MS									
	21 – 25		<b>33.4125</b>	CT-K-VSH M32x21-25,5 MS									
4	9.5 – 12.5	25	<b>33.4120</b>	CT-K-VSH M25x9,5-12,5 MS	30	5 <sup>1)</sup>	<b>33.3175</b>	CT-CH5-T/4xM25					
	10 – 17		<b>33.4126</b>	CT-K-VSH M25x10-17 MS	28								
	16 – 20.5		<b>33.4122</b>	CT-K-VSH M25x16-20,5 MS	30								
5	9.5 – 12.5	25	<b>33.4120</b>	CT-K-VSH M25x9,5-12,5 MS	30	6 <sup>1)</sup>	<b>33.3186</b>	CT-CH6-T/6xM25 <sup>2)</sup>					
	10 – 17		<b>33.4126</b>	CT-K-VSH M25x10-17 MS	28								
	16 – 20.5		<b>33.4122</b>	CT-K-VSH M25x16-20,5 MS	30								

<sup>1)</sup> Rated as IP00, IP65 available on request

<sup>2)</sup> Close one gland opening with cap (not provided).



## HOUSINGS WITH SPACE SAVING LOCKING


# Coupler hood

Coupler hoods can be combined with surface mount housing. Available with side or top cable entry.


### Note for sizes 2, 3, 4:

For white housing, please add the color code number 29, e.g. 33.2362-29. Other colors available upon request.

#### CT-CH...-S/SSL



#### CT-CH...-T/SSL



Size	Order No.	Type	IP67	Cable entry		Sizes (mm)				Standard color
				Side	Top	A1	A2	A3	A6	
2	35.1242	CT-CH2-S/SSL	x	x		74	44	70	M32	29
	35.1232	CT-CH2-T/SSL	x		x					
3	35.1243	CT-CH3-S/SSL	x	x		94	44	76	M32	29
	35.1233	CT-CH3-T/SSL	x		x					
4	35.1244	CT-CH4-S/SSL	x	x		120	44	78	M32	29
	35.1234	CT-CH4-T/SSL	x		x					


# Surface mount housing

Surface mount housings are used for bottom cable entry. They are combined with coupler hoods.

**Note for sizes 2, 3, 4:**

For white housing, please add the color code number 29, e.g. 33.2362-**29**. Other colors available upon request.

CT-SM...



Size	Order No.	Type	IP67	Sizes (mm)					Standard color
				A1	A2	A3	A4		
							Locked	Unlocked	
2	35.1252	CT-SM2/SSL	x	94	45	29	3.3	26	■ 29
3	35.1253	CT-SM3/SSL	x	114	45	29	7.8	31	■ 29
4	35.1254	CT-SM4/SSL	x	141	45	29	3.9	30	■ 29


# Park stations

Used for parking coupler hoods when they are not connected to mount housings. Include CombiTac direct frames.


**Note for sizes 2, 3, 4:**

For white housing, please add the color code number 29, e.g. 33.2362-**29**. Other colors available upon request.

**CTD-PS...-SM/SSL/P**



**CTD-PS...-SM/SSL/S**




Size	Order No.	Type	IP67	Pin end pieces	Socket end pieces	Sizes (mm)					Standard color
						A1	A2	A3	A4		
								Locked	Unlocked		
2	35.1762	CTD-PS2-SM/SSL/P	x	x		94	45	29	3.3	26	■ 29
	35.1752	CTD-PS2-SM/SSL/S	x		x						
3	35.1763	CTD-PS3-SM/SSL/P	x	x		114	45	29	7.8	31	■ 29
	35.1753	CTD-PS3-SM/SSL/S	x		x						
4	35.1764	CTD-PS4-SM/SSL/P	x	x		141	45	29	3.9	30	■ 29
	35.1754	CTD-PS4-SM/SSL/S	x		x						



# Replacement seals

Replacement housing seals made of NBR can be reordered.



CT-DDI-SM...




CT-PDI-SM...

Size	Order No.	Type	Description
2	33.2782	CT-DDI-SM2	Upper seal
3	33.2783	CT-DDI-SM3	
4	33.2784	CT-DDI-SM4	
2	33.2792	CT-PDI-SM2	Lower seal
3	33.2793	CT-PDI-SM3	
4	33.2794	CT-PDI-SM4	

ALUMINUM HOUSING IP68/69K


Coupler hood



The all-round contact of the two housing halves of the IP68/69K enclosures provides a 360° shielding against electromagnetic influence according to VG 95373-41.


Size	Order No.	Type	Cable entry		Sizes (mm)			
			Side	Top	A1	A2	A3	A6
1	33.6871	CT-TG1-S IP68 HE	×		132	58	100.5	M32
	33.6881	CT-TG1-G IP68 HE		×				
2	33.6872	CT-TG2-S IP68 HE	×		144	58	100.5	M32
	33.6882	CT-TG2-G IP68 HE		×				
3	33.6873	CT-TG3-S IP68 HE	×		164	58	110.5	M40
	33.6883	CT-TG3-G IP68 HE		×				
4	33.6874	CT-TG4-S IP68 HE	×		191	58	110.5	M40
	33.6884	CT-TG4-G IP68 HE		×				

Surface mount housing



Size	Order No.	Type	Sizes (mm)		
			A1	A2	A3
1	33.6851	CT-AG1 IP68 HE	132	58	29.5
2	33.6852	CT-AG2 IP68 HE	144	58	29.5
3	33.6853	CT-AG3 IP68 HE	164	58	29.5
4	33.6854	CT-AG4 IP68 HE	191	58	29.5

# Pedestal mount housing



Size	Order No.	Type	Sizes (mm)			
			A1	A2	A3	A6
1	33.6861	CT-SG1 IP68 HE	156	80	100.5	2×M25
2	33.6862	CT-SG2 IP68 HE	169	80	100.5	2×M32
3	33.6863	CT-SG3 IP68 HE	189	80	111.5	2×M32
4	33.6864	CT-SG4 IP68 HE	216	80	111.5	2×M40

# Protective cap



Size	Order No.	Type
1	33.6891	CT-PC1 IP68 HE
2	33.6892	CT-PC2 IP68 HE
3	33.6893	CT-PC3 IP68 HE
4	33.6894	CT-PC4 IP68 HE


## PLASTIC HOUSING IP65

# Plastic DIN housing

The plastic housing is primarily intended for industrial use or for applications where a high resistance to chemical environmental influences is required.

In addition, the plastic housing is mechanically robust.

As the housing is made of antistatic thermoplastic material, there is no need for additional grounding.



### Technical data

Housing material	Thermoplastic
Housing seal	Elastomer
Locking element	Thermoplastic
Degree of protection mated/locked	IP65


Plastic housing – Resistance to aggressive media		
	Resistant	Limited resistance
1-Pentanol		x
Alum	x	
Amide, aqueous	x	
Ammonia gas		x
Ammonia, 10 % aqueous solution	x	
Ammonium acetate	x	
Ammonium carbonate	x	
Ammonium chloride	x	
Ammonium nitrate	x	
Ammonium phosphate	x	
Ammonium sulfate	x	
Aniline		x
Asphalt		x
Beer	x	
Borated water	x	
Borax		x
Boric acid, 10 % aqueous solution	x	
Boric acid	x	
Butane gas		x
Butane, liquid		x
Calcium chloride, 10 % aqueous solution	x	
Calcium chloride	x	
Calcium nitrate	x	
Calcium sulfate	x	
Chlorinated lime, diluted	x	
Copper sulfate, 10 % aqueous solution	x	
Cresol acids		x
Cresol solution		x
Cutting oil		x
Cyclohexane		x
Diesel		x
Diisononyl phthalate	x	
Di-Octyl-Phthalate	x	
Diluted glucose	x	
Diluted glycerol	x	
Diluted glycol	x	
Diluted phenol		x
Ethanol, non-denaturized	x	
Ethylene glycol or propylene glycol	x	
Fatty acids	x	
Fruit juices	x	
Gasoline		x

Plastic housing – Resistance to aggressive media		
	Resistant	Limited resistance
Glycerol	x	
Grinding oil		x
Gypsum (see calcium sulfate)	x	
Heptane		x
Hexane		x
Hydrogen sulfide		x
Ink	x	
Isopropyl alcohol		x
Lactic acid	x	
Linseed oil	x	
Lubricating oil	x	
Mercury	x	
Methanol, diluted by 50 %		x
Mineral oil	x	
Mineral spirits (Avio)		x
Mineral-based oil	x	
Mothballs		x
Motor oil		x
n-Butanol	x	
Naphthalene		x
Octane		x
Oil IRM 901, 20 °C	x	
Oil IRM 902, 20 °C		x
Oil IRM 903, 20 °C		x
Oil		x
Oleic acid	x	
Oxalic acid	x	
Paraffin oil	x	
Petroleum	x	
Phthalate	x	
Potassium carbonate	x	
Potassium chlorate	x	
Potassium chloride	x	
Potassium chromate		x
Potassium cyanide, aqueous solution	x	
Potassium iodide		x
Potassium nitrate		x
Potassium persulfate		x
Potassium sulfate		x
Seawater	x	
Silicone oil	x	
Soap solution		x


Plastic housing – Resistance to aggressive media		
	Resistant	Limited resistance
Sodium bicarbonate	x	
Sodium carbonate	x	
Sodium chlorate	x	
Sodium chloride (table salt)	x	
Sodium hydrogen sulfate, aqueous solution	x	
Sodium hydroxide 12.5 % (alkaline solution)		x
Sodium nitrate	x	
Sodium nitrite		x
Sodium perborate	x	
Sodium phosphate	x	
Sodium silicate	x	
Sodium sulfate	x	
Sodium sulfide	x	
Sodium thiosulfate (fixing salt/developing film)	x	
Solution for developing photographs	x	
Stearic acid	x	
Succinic acid	x	
Sulfur dioxide		x
Sulfur	x	
Table salt, aqueous solution	x	
Tallow	x	
Tartaric acid	x	
Tar		x
Transformer oil	x	
Tricresyl phosphate	x	
Turpentine substitute		x
Urea, diluted	x	
Urine	x	
Vegetable oil	x	
Water	x	
White spirits (isopropanol and ethanol)		x

# Coupler hood

CT-TG1-S TP




CT-TG...-G TP




Size	Order No.	Type	Cable entry		Sizes (mm)					
			Side	Top	A1	A2	A3	A6	A7	A8
1 <sup>1)</sup>	33.6011	CT-TG1-S TP	x		63	46	71.5	M32	73	86.5
	33.6021	CT-TG1-G TP		x						
2	33.6012	CT-TG2-S TP	x		76	46	71.5	M32	73	86.5
	33.6022	CT-TG2-G TP		x						
3	33.6013	CT-TG3-S TP	x		96.5	46	75.5	M32	79	90.5
	33.6023	CT-TG3-G TP		x						
4	33.6014	CT-TG4-S TP	x		123	46	75.5	M32	79	90.5
	33.6024	CT-TG4-G TP		x						

# Surface mount housing

CT-AG1 TP



CT-AG...TP




Size	Order No.	Type	Sizes (mm)		
			A1	A2	A3
1 <sup>1)</sup>	33.6041	CT-AG1 TP	83	46	27
2	33.6042	CT-AG2 TP	96	46	27
3	33.6043	CT-AG3 TP	116	46	27
4	33.6044	CT-AG4 TP	143	46	27


<sup>1)</sup> Size 1: housings only have a single locking device.

# Pedestal mount housing

CT-SG1 TP



CT-SG...TP



Size	Order No.	Type	Sizes (mm)			
			A1	A2	A3	A6
1 <sup>1)</sup>	33.6601	CT-SG1 TP	82	57	73	M32
2	33.6602	CT-SG2 TP	94	57	80	M32
3	33.6603	CT-SG3 TP	117	57	80	M32
4	33.6604	CT-SG4 TP	144	57	80	M32

# Protective cap

CT-SD-AG1 TP



CT-SD-AG... TP



Size	Order No.	Type
1 <sup>1)</sup>	33.6031	CT-SD-AG1 TP
2	33.6032	CT-SD-AG2 TP
3	33.6033	CT-SD-AG3 TP
4	33.6034	CT-SD-AG4 TP

<sup>1)</sup> Size 1: housings only have a single locking device.



CRIMPING PLIERS

Crimping the electric contacts



Pos.	Order No.	Type	Conductor cross section	Description	MA
a	33.3900	CTD-M-CZ		Crimping pliers	
b	33.3910	MES-CZ-CTD1	0.14 – 0.75 mm <sup>2</sup>	Locator	MA417 MA419
c	33.3911	MES-CZ-CTD1,5	0.75 – 1.5 mm <sup>2</sup>	Locator	
d	33.3912	MES-CZ-CTD3	2.5 – 4 mm <sup>2</sup>	Locator	
e	18.3700	M-PZ13		Crimping pliers	
f	18.3702	MES-PZ-TB 8/10	10 mm <sup>2</sup>	Crimping die	
g	18.3703	MES-PZ-TB 9/16	16 mm <sup>2</sup>	Crimping die	MA224
h	18.3704	MES-PZ-TB11/25	25 mm <sup>2</sup>	Crimping die	
i	18.3707	MPS-PZ13		Test insert	
j	18.3708	MALU-PZ13		Round test rod	
k	18.3710	M-PZ-T2600		Crimping pliers with case	
l	18.3711	TB8-17	10 mm <sup>2</sup> + 70 mm <sup>2</sup>	Crimping die	
m	18.3712	TB9-13	16 mm <sup>2</sup> + 35 mm <sup>2</sup>	Crimping die	MA213-01 MA226
n	18.3713	TB11-14,5	50 mm <sup>2</sup>	Crimping die	
o	18.3714	TB7-20	95 mm <sup>2</sup>	Crimping die	
p	33.3930	CT-CP		Crimping pliers	
q	33.3931	CT-I-CP-4	4 mm <sup>2</sup>	Crimping die	MA417 MA420
r	33.3932	CT-I-CP-6	6 mm <sup>2</sup>	Crimping die (standard option)	

APPENDIX

# Derating diagrams

The following derating curves are based on measurements according to IEC 60512-5-2:2002.

The measurements were carried out on a fully assembled frame size 4. The wires were unbundled, free in air. A reduction factor of 0.9 (derating) was applied to the measured currents.

These diagrams show examples of the rated current as a function of the various ambient temperatures up to 125 °C.

The derating curves for several bundled wires from example 2 onwards were created using the conversion factors from IEC 60364-5-52:2009 table B.52.17.


If a CombiTac is used to equip machines, the standard IEC 60204-1:2016 applies.

**Note:**

The legend of the derating diagrams does not indicate the number of circuits, but the number of conductors. This differs from the IEC 60364-5-52:2009 standard, which always refers to the number of circuits. For example, if IEC refers to a 95 mm<sup>2</sup> circuit, this is written as 2 x 95 mm<sup>2</sup>.

**Ø 10 mm modul:**


Derating curves for wires with cross sections of 35 mm<sup>2</sup>, 50 mm<sup>2</sup>, 70 mm<sup>2</sup> and 95 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.



**Ø 7 mm modul:**

Derating curves for 2, 4 and 8 bundled wires each with the cross sections 16 mm<sup>2</sup> and 25 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.


The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.



**Ø 7 mm modul:**

Derating curves for 2, 4 and 8 bundled wires each with the cross sections 6 mm<sup>2</sup> and 10 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.


The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.



**Ø 4 mm modul:**

Derating curves for 2 and 6 bundled wires with the cross sections 4 mm<sup>2</sup>, 6 mm<sup>2</sup> and 10 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.


The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.



**Ø 3 mm modul:**

Derating curves for 3 and 9 bundled wires with the cross sections 2.5 mm<sup>2</sup> and 4 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.


The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.



**Ø 1,5 mm modul:**

Derating curves for 5 and 15 bundled wires with the cross sections 0.75 mm<sup>2</sup>, 1 mm<sup>2</sup> and 1.5 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.


The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.



**Ø 1 mm modul:**


Derating curves for 7 and 28 bundled wires each with the cross sections 0.14 mm<sup>2</sup>, 0.25 mm<sup>2</sup> and 0.5 mm<sup>2</sup>. The maximum permissible conductor temperature is 125 °C.

The curves were calculated according to IEC 60364-5-52:2009 table B.52.17.





# Flow, head loss diagrams, and sliding forces

Test conditions CT-...-RCT03/6




Compressed air:

Under standard conditions 0 °C, 1013 mbar


Socket	Flow direction	Plug	Max. sliding force		Input pressure	Tube-Ø
			0 bar	15 bar		
CT-BV-RCT03/6 <sup>1)</sup>	 	CT-S-RCT03/6	12 N	35 N	6 bar	6 mm

Test conditions CT-...-RCT03/6



Compressed air:

Under standard conditions 0 °C, 1013 mbar

Socket	Flow direction	Plug	Max. sliding force		Input pressure	Tube-Ø
			0 bar	15 bar		
CT-B-RCT03/6		CT-S-RCT03/6	10 N	33 N	6 bar	6 mm

<sup>1)</sup> Without shut-off valve

# Technical information

## Sliding forces

The average sliding force of a CombiTac connector is the sum of all average sliding forces of the single contacts. The stated values are guideline values, and may be reduced by 20 – 30 % after a number of mating cycles.

## Locking cycles DIN housing

Max. 500 locking cycles without lubrication. For up to 5,000 locking cycles, a lubrication must be executed. See note about lubrication, assembly instructions MA213.

## Manual mating speed:

CombiTac is designed to be mated at a speed of 600 mm/min. Plugging force is equal to 1.5 times the sliding force.

## Rated current

The rated current is the current, preferably at an ambient temperature of 40 °C, that each contact of the connector or connector device can carry simultaneously and permanently (without interruption).

## Bundled wires

If the CombiTac is used together with bundled wires, a reduction factor must be applied to the wires. The derating diagrams on pages 66 – 69 show various examples for bundled copper wires with different cross sections that are suitable for use with CombiTac.

The listed wires are heat-resistant up to 125 °C. A conversion factor according to IEC 60364-5-52:2009, table B52.17 must be used for a certain number of bundled wires or wire types.

## Rated voltage (IEC 60664-1:2020)

Value of voltage assigned by the manufacturer, to a component, device, or equipment and to which operation and performance characteristics are referred. Equipment may have more than one rated voltage value or may have a rated voltage range.

The rated voltages listed below correlate normatively with the following impulse withstand voltages. This is subject to the overvoltage category to be met.

## Overvoltage categories

The concept of overvoltage categories is used for equipment energized directly from the low-voltage mains.

**CAT I:** Equipment with an impulse withstand voltage corresponding to overvoltage category I shall not have direct connection to a mains supply.

Measures shall be taken to ensure that the temporary overvoltages that could occur are sufficiently limited so that their peak value does not exceed the relevant rated impulse voltage.

Unless the circuits are designed to take the temporary overvoltages into account, equipment of overvoltage category I cannot be directly connected to the mains supply. Examples of such equipment are devices with electronic circuits and corresponding protection level.

**CAT II:** Equipment of the overvoltage category II is energy consuming equipment to be supplied from the fixed installation.

Examples of such equipment are appliances, portable tools, and other household and similar loads.

IEC 60664-1:2020			IEC 61984:2008	
Rated voltage	Impulse withstand voltage		Test voltage: r.m.s withstand voltage 1 min, 50/60 Hz	
	Overvoltage category II	Overvoltage category III	Overvoltage category II	Overvoltage category III
< 51 V	500 V	800 V	370 V	500 V
51 V – 100 V	800 V	1500 V	500 V	840 V
101 V – 150 V	1500 V	2500 V	840 V	1390 V
151 V – 300 V	2500 V	4000 V	1390 V	2210 V
301 V – 600 V	4000 V	6000 V	2210 V	3310 V
601 V – 1000 V	6000 V	8000 V	3310 V	4260 V

**CAT III:** Equipment of overvoltage category III is equipment in fixed installations and for cases where the reliability and the availability of the equipment is subject to special requirements.

Examples of such equipment are switches in the fixed installation and equipment for industrial use with a permanent connection to the fixed installation.

**Protective conductor PE (IEC 61140:2016)**

Conductor provided for purposes of safety, for example protection against electric shock. Marking of the protective bonding terminal with letter PE, or color combination green-yellow, or graphical symbol. Connect this terminal to the protective-equipotential-bonding system of the installation.

**Pollution degree 1 (IEC 60664-1:2020)**

No pollution or only dry, non-conductive pollution occurs. The pollution has no influence.

**Pollution degree 2 (IEC 60664-1:2020)**

Only non-conductive pollution occurs except that occasionally a temporary conductivity caused by condensation is to be expected.

**Pollution degree 3 (IEC 60664-1:2020)**

Conductive pollution occurs or dry non-conductive pollution occurs which becomes conductive due to condensation which is to be expected.

**Connector resistance**

The connector resistance is determined by means of the voltage drop, measured between the lead terminations of the pin and socket. The values given are average values determined at rated current.

**Mating cycles**

Mating cycles tests for CombiTac parts are performed under typical laboratory environmental conditions.

**Limiting temperature**

The limiting temperatures specified in this catalog apply to CombiTac connectors in mated condition.

**RoHS Conformity**

**European Directive 2011/65/EU (RoHS 2)**

**Commission Delegated Directive (EU) 2015/863 (RoHS 3)**

For further information please visit our website

[www.staubli.com/global/en/electrical-connectors/downloads/certificates/rohs-conformity.html](http://www.staubli.com/global/en/electrical-connectors/downloads/certificates/rohs-conformity.html)



# Safety notes

## Protection against electric shock

A connector shall be so designed that, after mounting, its live parts are not accessible by the IEC test finger in accordance with clause 5 of IEC 60529:2013 using a test force of 20 N. These products are designed to be built into a housing that guarantees the relevant IP protection for cable connections (at least IP2X). Protection against electric shock must be provided by the end product and ensured by the users themselves. This requirement does not apply to a connector operated with a safety extra-low voltage (SELV) of a maximum AC 50 V eff. or DC 120 V. The customer must take appropriate measures when fitting the connectors to ensure that the cable connection is protected against tension and twisting and is responsible for correct implementation of the contact-protection measures.

Connecting and disconnecting when live is permitted.

Connecting and disconnecting under load is not permitted.

## Enclosure

An enclosed connector is a connector for which the protection against electric shock is ensured by the housing of the connector itself. An unenclosed connector is a connector for which the protection against electric shock is provided by the enclosure of the equipment in which the connector is mounted.

In relation to the direction of power flow, connectors should be incorporated in the circuit wiring in such a way that pins that can be touched are not live in the unmated state (IEC 61984:2008).

## Protection wall

In order to meet the requirement for protection against accessibility of live parts during connecting and disconnecting, CombiTac is provided with a specially designed protection wall.

## Electrical contacts in close proximity to connectors for liquids and gases

Defect electrical contacts or connectors that leak gas or liquids can be a safety hazard to personnel, the environment, as well as affecting the proper function of the system. It is the responsibility of the end-user to ensure that both safety and proper function in the end-use is guaranteed. The result of a risk analysis requires that the end-user of CombiTac connectors must ensure the following:

- All relevant national and international standards and regulations must be complied with in the end-use.
- Field-tested techniques must be applied and, a risk assessment must be carried out in order to identify and reduce the risks.
- The use of flammable or explosive liquids or gases is prohibited.
- Exclusively CT-...SCT couplings with both male and female-sided locking systems are permitted to be used for liquids.
- Automatic disconnection of power supply in the event of indirect contact, overload, or short circuit is required according to IEC 60364-4-41:2017.
- If the voltage is higher than AC 50 V or DC 120 V, all simultaneously accessible conductive parts that do not carry current during normal operation must be connected to the protective conductor (protective equipotential bonding according to IEC 60364-4-41:2017).
- If the voltage is higher than AC 50 V or DC 120 V, all electric circuits have to be protected by a residual-current-operated protective device (RCD) with a rated residual operating current not exceeding 30 mA according to IEC 60364-4-41:2017.
- Connecting or disconnecting under load or live is not allowed (connector without breaking capacity according to IEC 61984:2008).

- On permanently fixed installations, electrical contacts have to be placed above liquid couplings.
- In CombiTac housing applications, the housing has to be connected to the protective conductor according to IEC 60364-4-41:2017.
- The fluid couplings must be replaced if a leak is detected.

## Underwriters Laboratories


### Standard UL 1977 states:

A connector operated above 30 V (42 V peak) up to AC/DC 600 V intended for usage external to the end equipment shall have live parts protected against exposure to contact by persons when assembled, installed, and mated as intended, as determined by the use of the articulate probe with web stop (UL test finger).

Mating devices operated above 30 V up to AC/DC 600 V intended for usage external to the end equipment shall not have exposed live contacts during engagement or withdrawal, as determined by the use of the articulate probe with web stop (UL test finger).

# Safety situation for CombiTac connectors

Connecting and disconnecting when CombiTac is isolated from supply




Connecting and disconnecting when live is permitted.

**With protection wall**



Connecting and disconnecting under load is not permitted.




**⚠ Attention**

When disconnected, the socket side is touch protected, i.e. has IP2X protection


according to IEC 60529 (test finger). See also page 73, section "Underwriters Laboratories standard UL 1977".

Connecting and disconnecting when live and under load not permitted.

**With or without protection wall**



Panel-mounted version



The protection against electric shock is provided by the enclosure of the equipment in

which it is installed. This is provided by the CombiTac end-user.

# Index

Type	Page
CT-AG1 IP68 HE	58
CT-AG1 TP	63
CT-AG2 IP68 HE	58
CT-AG2 TP	63
CT-AG3 IP68 HE	58
CT-AG3 TP	63
CT-AG4 IP68 HE	58
CT-AG4 TP	63
CT-B-COAX-RG58	31
CT-B-COAX-RG316/U	31
CT-B-COAX-SMA	31
CT-B-RCT03/4	35
CT-B-RCT03/6	35
CT-BV-RCT03/4	35
CT-BV-RCT03/6	35
CT-CH1-S	42
CT-CH1-T	42
CT-CH2-S	42
CT-CH2-S/PW	45
CT-CH2-S/PW-PC	45
CT-CH2-S/SSL	54
CT-CH2-T	42
CT-CH2-T/PW	45
CT-CH2-T/PW-PC	45
CT-CH2-T/SSL	54
CT-CH3-S	42
CT-CH3-S/PW	45
CT-CH3-S/PW-PC	45
CT-CH3-S/SSL	54
CT-CH3-T	42
CT-CH3-T/PW	45
CT-CH3-T/PW-PC	45
CT-CH3-T/SSL	54
CT-CH4-S	42
CT-CH4-S/PW	45
CT-CH4-S/PW-PC	45
CT-CH4-S/SSL	54
CT-CH4-T	42
CT-CH4-T/PW	45
CT-CH4-T/PW-PC	45
CT-CH4-T/SSL	54
CT-CH5-S	42

Type	Page
CT-CH5-S/PW	45
CT-CH5-S/PW-PC	45
CT-CH5-T	42
CT-CH5-T/PW	45
CT-CH5-T/PW-PC	45
CT-CH6-S	42
CT-CH6-S/PW	45
CT-CH6-S/PW-PC	45
CT-CH6-T	42
CT-CH6-T/PW	45
CT-CH6-T/PW-PC	45
CT-CHG1-T	43
CT-CHG2-T	43
CT-CHG2-T/PW	43
CT-CHG3-T	43
CT-CHG3-T/PW	43
CT-CHG4-T	43
CT-CHG4-T/PW	43
CT-CHG5-T	43
CT-CP	65
CTD-10-SRTU/43	11
CTD-C1,5-5/P	20
CTD-C1,5-5/S	20
CTD-C1-7/P	22
CTD-C1-7/S	22
CTD-C1-21/P	22
CTD-C1-21/S	22
CTD-C3-2+PE/P	18
CTD-C3-2+PE/S	18
CTD-C3-3/P	18
CTD-C3-3/S	18
CTD-C7-2/P	12
CTD-C7-2/S	12
CTD-C10-1/P	10
CTD-C10-1/S	10
CTD-C-C4-2/P	14
CTD-C-C4-2/P PE	14
CTD-C-C4-2/S	14
CTD-C-C4-2/S PE	14
CTD-CP-2/P	34
CTD-CP-2/S	34
CTD-CUDM-SH	30, 32

Type	Page
CTD-DIP3,5	36
CT-DDI-SM2	51, 57
CT-DDI-SM3	51, 57
CT-DDI-SM4	51, 57
CTD-FH1/P	37
CTD-FH1/S	37
CTD-FH2/P	37
CTD-FH2/S	37
CTD-FH3/P	37
CTD-FH3/S	37
CTD-FH4/P	37
CTD-FH4/S	37
CTD-FP1/P	37
CTD-FP1/S	37
CTD-FP2/P	37
CTD-FP2/S	37
CTD-FP3/P	37
CTD-FP3/S	37
CTD-FP4/P	37
CTD-FP4/S	37
CTD-LMFB-P/0,14-0,25	24
CTD-LMFB-P/0,25-0,75	24
CTD-LMFB-P1/0,14-0,25 AU	25
CTD-LMFB-P1/0,25-0,75 AU	25
CTD-LMFB-S/0,14-0,25	24
CTD-LMFB-S/0,25-0,75	24
CTD-LMFB-S1/0,14-0,25 AU	25
CTD-LMFB-S1/0,25-0,75 AU	25
CTD-M-CZ	65
CTD-NET-1/P	26
CTD-NET-1/S	26
CTD-P1/0,14-0,25 AU	23
CTD-P1/0,25-0,75 AU	23
CTD-P1,5/0,75-1,5 AU	21
CTD-P3/2,5-4 AU	19
CTD-P3/2,5-4/PE AU	19
CTD-P4/4 IP2X AG	17
CTD-P4/4-S IP2X AG	17
CTD-P4/6 IP2X AG	17
CTD-P4/6-S IP2X AG	17
CTD-P4/10 IP2X AG	17
CTD-P4/10-S IP2X AG	17

Type	Page
CTD-P7/6 IP2X AG	13
CTD-P7/10 IP2X AG	13
CTD-P7/16 IP2X AG	13
CTD-P7/25 IP2X AG	13
CTD-P10/35 IP2X AG	11
CTD-P10/50 IP2X AG	11
CTD-P10/70 IP2X AG	11
CTD-P10/95 IP2X AG	11
CTD-P/COAX58	33
CTD-PS1/PC-SM/S	51
CTD-PS1-SM/P	51
CTD-PS1-SM/S	51
CTD-PS2/PC-SM/S	51
CTD-PS2-SM/P	51
CTD-PS2-SM/S	51
CTD-PS2-SM/SSL/P	56
CTD-PS2-SM/SSL/S	56
CTD-PS3/PC-SM/S	51
CTD-PS3-SM/P	51
CTD-PS3-SM/S	51
CTD-PS3-SM/SSL/P	56
CTD-PS3-SM/SSL/S	56
CTD-PS4/PC-SM/S	51
CTD-PS4-SM/P	51
CTD-PS4-SM/S	51
CTD-PS4-SM/SSL/P	56
CTD-PS4-SM/SSL/S	56
CTD-PS5/PC-SM/S	51
CTD-PS5-SM/P	51
CTD-PS5-SM/S	51
CTD-PS6/PC-SM/S	51
CTD-PS6-SM/P	51
CTD-PS6-SM/S	51
CTD-RC4	14
CTD-RC7	12
CTD-RC10	10
CTD-RC-UDM-COAX	30
CTD-RC-UDM-NET	26
CTD-RC-UDM-RJ45	29, 32
CTD-RJ45-1/P	29
CTD-RJ45-1/S	29
CTD-S1/0,14-0,25 AU	23

Type	Page
CTD-S1/0,25-0,75 AU	23
CTD-S1,5/0,75-1,5 AU	21
CTD-S3/2,5-4 AU	19
CTD-S4/4 AG	17
CTD-S4/6 AG	17
CTD-S4/10 AG	17
CTD-S7/6 AG	13
CTD-S7/10 AG	13
CTD-S7/16 AG	13
CTD-S7/25 AG	13
CTD-S10/35 AG	11
CTD-S10/50 AG	11
CTD-S10/70 AG	11
CTD-S10/95 AG	11
CTD-S/COAX58	33
CT-I-CP-4	65
CT-I-CP-6	65
CT-K-VSH M25x9,5-12,5 MS	52
CT-K-VSH M25x10-17 MS	52
CT-K-VSH M25x16-20,5 MS	52
CT-K-VSH M32x14-17 MS	52
CT-K-VSH M32x17-21 MS	52
CT-K-VSH M32x21-25,5 MS	52
CT-NET-AWZ	27
CT-NET-BP1 ET/0,14-0,75 AU	27
CT-NET-BS	27
CT-NET-SP1/0,14-0,75 AU	27
CT-PC1 IP68 HE	59
CT-PC2 IP68 HE	59
CT-PC3 IP68 HE	59
CT-PC4 IP68 HE	59
CT-PDI-SM2	51, 57
CT-PDI-SM3	51, 57
CT-PDI-SM4	51, 57
CT-PM1	49
CT-PM1-PC	49
CT-PM2	49
CT-PM2-PC	49
CT-PM2/PW	49
CT-PM3	49
CT-PM3-PC	49
CT-PM3/PW	49

Type	Page
CT-PM4	49
CT-PM4-PC	49
CT-PM4/PW	49
CT-PM5	49
CT-PM5-PC	49
CT-PM5/PW	49
CT-PM6	49
CT-PM6-PC	49
CT-S-COAX-RG58	31
CT-S-COAX-RG316/U	31
CT-S-COAX-SMA	31
CT-SD-AG1 TP	64
CT-SD-AG2 TP	64
CT-SD-AG3 TP	64
CT-SD-AG4 TP	64
CT-SG1 IP68 HE	59
CT-SG1 TP	64
CT-SG2 IP68 HE	59
CT-SG2 TP	64
CT-SG3 IP68 HE	59
CT-SG3 TP	64
CT-SG4 IP68 HE	59
CT-SG4 TP	64
CT-SM1	47
CT-SM1-PC	47
CT-SM2	47
CT-SM2-PC	47
CT-SM2/PW	47
CT-SM2/SSL	55
CT-SM3	47
CT-SM3-PC	47
CT-SM3/PW	47
CT-SM3/SSL	55
CT-SM4	47
CT-SM4-PC	47
CT-SM4/PW	47
CT-SM4/SSL	55
CT-SM5	47
CT-SM5-PC	47
CT-SM5/PW	47
CT-SM6	47
CT-SM6-PC	47

Type	Page
CT-S-RCT03/4	35
CT-S-RCT03/6	35
CT-TG1-G IP68 HE	58
CT-TG1-G TP	63
CT-TG1-S IP68 HE	58
CT-TG1-S TP	63
CT-TG2-G IP68 HE	58
CT-TG2-G TP	63
CT-TG2-S IP68 HE	58
CT-TG2-S TP	63
CT-TG3-G IP68 HE	58
CT-TG3-G TP	63
CT-TG3-S IP68 HE	58
CT-TG3-S TP	63
CT-TG4-G IP68 HE	58
CT-TG4-G TP	63
CT-TG4-S IP68 HE	58
CT-TG4-S TP	63
MALU-PZ13	65
MES-CZ-CTD1	65
MES-CZ-CTD1,5	65
MES-CZ-CTD3	65
MES-PZ-TB 8/10	65
MES-PZ-TB 9/16	65
MES-PZ-TB11/25	65
MPS-PZ13	65
M-PZ13	65
M-PZ-T2600	65
TB7-20	65
TB8-17	65
TB9-13	65
TB11-14,5	65





● Stäubli Units ○ Representatives/Agents

# Global presence of the Stäubli Group

[www.staubli.com](http://www.staubli.com)